



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	14.00	—
E	—	22.00	—
v	—	—	0.20
w	—	—	—
A	1.80	2.02	2.24
A ₁	0.61	0.69	0.77
e	—	1.27	—
b	0.82	0.88	0.94
x	—	—	0.30
y	—	—	0.20
y ₁	—	—	0.35
SE	—	—	—
SE	—	—	—
ZD	—	—	—
ZE	—	—	—