



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	14.00	—
E	—	22.00	—
v	—	—	0.20
w	—	—	—
A	1.78	1.98	2.18
A1	0.58	0.66	0.74
e	—	1.27	—
b	0.84	0.90	0.96
x	—	—	0.30
y	—	—	0.20
y1	—	—	0.35
S _D	—	—	—
S _E	—	—	—
Z _D	—	—	—
Z _E	—	—	—