



Reference Symbol	Dimension in Millimeters		
	Min	Nom	Max
D	—	31.0	—
E	—	31.0	—
v	—	—	0.20
w	—	—	0.30
A	—	—	2.0
A ₁	0.4	0.5	0.6
e	—	1.0	—
b	0.50	0.60	0.70
x	—	—	0.10
y	—	—	0.15
y ₁	—	—	0.35
S _D	—	—	—
S _E	—	—	—
Z _D	—	1.5	—
Z _E	—	1.5	—